

HOLROYD

BESPOKE SURFACE HEATING ELEMENTS

APPLICATIONS:

The HIBC/A container heater is designed to heat products stored in 1000 litre Bag-in-Box intermediate bulk containers. Manufactured from the highest quality materials, the HIBC/A is designed for placement below the liner of the intermediate bulk container. This is delivered with a digital temperature controller providing simple and accurate temperature control. The heater is ideal for providing direct and uniform heating to products ranging from glucose and wax to honey and shampoo.

MAIN POINTS:

- Drop In/Removable Base Heater
- Silicone Rubber Class II Double Insulated Construction
- Integral PTC Temperature Sensor
- In-Built Residual Current Device
- 0-150°C Electronic Controller
- Standard 1000L Sizes
- Full Design & Manufacturing Service
- Direct and Uniform Heating
- Copper Nickel Wire and Silicone Fibreglass Sheet
- IP64 Protection



QUALITY



RELIABILITY



CREATIVITY



SERVICE



COMMUNITY

+44 (0)1799 523177

SALES@HOLROYDCOMPONENTS.COM

HOLROYD COMPONENTS LTD
SHIRE HILL INDUSTRIAL ESTATE
SAFFRON WALDEN
ESSEX CB11 3AQ



WWW.HOLROYDCOMPONENTS.COM





QUALITY



RELIABILITY



CREATIVITY



SERVICE



COMMUNITY

CONSTRUCTION:

The HIBC/A silicone heater mat features a high temperature multi-stranded copper nickel resistance wire element, laminated between silicone fibreglass sheets to ensure a robust construction while also allowing product flexibility. The heater also incorporates a PTC temperature sensor between the silicone layers to offer the most accurate process temperature reading possible. This sensor connects to an electronic temperature controller via the heater power cable and provides accurate measurement and a fast response to temperature changes at the base of the IBC liner. This makes the heater suitable for both high energy absorbing products and highly viscous, temperature sensitive materials.

HEALTH AND SAFETY:

All HIBC/A heaters are manufactured to conform to the EEC low voltage and EMC directives and CE marked accordingly. It is advised that power to the heater be disconnected when the container is being filled, or upon installation or removal of the heater itself. It is recommended that the unit be operated in a dry environment with the container vented to avoid build up of internal pressure.

TECHNICAL DATA

SIZE	850 x 1035
RATING	110V 1800W or 230V 2700W
MATERIAL	Multi Stranded Copper Nickel Resistance Wire Laminated Between Silicone Rubber and Fibreglass Sheets
CONTROL	0-150°C Electronic Controller
POWER CABLE	2 Metre 1.5mm Diameter PVC

CONTROLLER

DIMENSIONS	200mm Long x 150mm Wide x 105mm High (Excluding Mounting bracket)
SENSOR INPUT	PTC1000 via 4 Pole Socket (output to heater)
SUPPLY VOLTAGE	110 or 230VAC
MAX POWER	3000W
ELECTRICAL PROTECTION	Residual Current Device

HIBC/A 2700W

